


ELECTROSTATIC FILTERS

DUSTFREE FILTERS

FEATURES:

- Easy installation and maintenance.
- Improves indoor air quality.
- Low resistance.
- High arrestance.
- Standard and custom sizes.
- Antimicrobial foam inner media.




P1055

OMEGA 1-IN. PART NO.	DIMENSIONS (in.)	OMEGA 2-IN. PART NO.	DIMENSIONS (in.)
DUF-100200	10 x 20 x 1	DUF2-100100	10 x 10 x 2
DUF-100240	10 x 24 x 1	DUF2-100200	10 x 20 x 2
DUF-120120	12 x 12 x 1	DUF2-100240	10 x 24 x 2
DUF-120200	12 x 20 x 1	DUF2-100300	10 x 30 x 2
DUF-120240	12 x 24 x 1	DUF2-120120	12 x 12 x 2
DUF-120280	12 x 28 x 1	DUF2-120200	12 x 20 x 2
DUF-120300	12 x 30 x 1	DUF2-120240	12 x 24 x 2
DUF-120360	12 x 36 x 1	DUF2-120250	12 x 25 x 2
DUF-13-1/8 x 21-5/8	13-1/8 x 21-5/8 x 1	DUF2-120300	12 x 30 x 2
DUF-140140	14 x 14 x 1	DUF2-120360	12 x 36 x 2
DUF-140200	14 x 20 x 1	DUF2-140140	14 x 14 x 2
DUF-140200B	14 x 20 x 1 - 4 pack	DUF2-140200	14 x 20 x 2
DUF-140220	14 x 22 x 1	DUF2-140240	14 x 24 x 2
DUF-140240	14 x 24 x 1	DUF2-140250	14 x 25 x 2
DUF-140250	14 x 25 x 1	DUF2-140300	14 x 30 x 2
DUF-140300	14 x 30 x 1	DUF2-150200	15 x 20 x 2
DUF-150200	15 x 20 x 1	DUF2-150250	15 x 25 x 2
DUF-16-1/2 x 21-5/8	16-1/2 x 21-5/8 x 1	DUF2-160160	16 x 16 x 2
DUF-16-3/8 x 21-1/2	16-3/8 x 21-1/2 x 1	DUF2-160200	16 x 20 x 2
DUF-160160	16 x 16 x 1	DUF2-160240	16 x 24 x 2
DUF-160200	16 x 20 x 1	DUF2-160250	16 x 25 x 2
DUF-160200B	16 x 20 x 1 - 4 pack	DUF2-160300	16 x 30 x 2
DUF-160240	16 x 24 x 1	DUF2-160320	16 x 32 x 2
DUF-160250	16 x 25 x 1	DUF2-160360	16 x 36 x 2
DUF-160250B	16 x 25 x 1 - 4 pack	DUF2-180180	18 x 18 x 2
DUF-160280	16 x 28 x 1	DUF2-180200	18 x 20 x 2
DUF-18-7/8 x 21-1/2	18-7/8 x 21-1/2 x 1	DUF2-180240	18 x 24 x 2
DUF-180180	18 x 18 x 1	DUF2-180250	18 x 25 x 2
DUF-180240	18 x 24 x 1	DUF2-180300	18 x 30 x 2
DUF-180250	18 x 25 x 1	DUF2-180360	18 x 36 x 2
DUF-200200	20 x 20 x 1	DUF2-190270	19 x 27 x 2
DUF-200200B	20 x 20 x 1 - 4 pack	DUF2-200200	20 x 20 x 2
DUF-200240	20 x 24 x 1	DUF2-200240	20 x 24 x 2
DUF-200250	20 x 25 x 1	DUF2-200250	20 x 25 x 2
DUF-200250B	20 x 25 x 1 - 4 pack	DUF2-200300	20 x 30 x 2
DUF-200280	20 x 28 x 1	DUF2-200320	20 x 32 x 2
DUF-200300	20 x 30 x 1	DUF2-210210	21 x 21 x 2
DUF-20 x 21-5/8	20 x 21-5/8 x 1	DUF2-240240	24 x 24 x 2
DUF-21-1/2 x 23-5/8/16	21-1/2 x 23-5/8/16 x 1	DUF2-240300	24 x 30 x 2
DUF-230280	23 x 28 x 1	DUF2-250250	25 x 25 x 2
DUF-240240	24 x 24 x 1		
DUF-240300	24 x 30 x 1		
DUF-250250	25 x 25 x 1		

SPECIAL SIZES

PART NO.	DESCRIPTION	
DUF-962025	Omega II Adjustable	20 X 25 X 1
DUF-962025B	Omega II Adjustable	20 x 25 x 1 - 4 pack
DUF-962430	Omega II Adjustable	24 x 30 x 1
DUF-1-CUSTOM	1 in. Omega Custom	Specify size in order notes
DUF-2-CUSTOM	2 in. Omega Custom	Specify size in order notes
DUF-95-CUSTOM1	1 in. Dustfree 95 Custom	Specify size in order notes
DUF-95-CUSTOM2	2 in. Dustfree 95 Custom	Specify size in order notes
DUF-95-CUSTOM3/4	3/4 in. Dustfree 95 Custom	Specify size in order notes
DUF-AG-CUSTOM	Allergy Gold Custom	Specify size in order notes
DUF-MA-1CUSTOM	Max Air Gold Custom	Specify size in order notes



P1055A

ELECTROSTATIC FILTERS

ALLERGY GOLD

PART NO.	DESCRIPTION	PART NO.	DESCRIPTION
DUF-AG-10101	10 x 10 x 1	DUF-AG-16301	16 x 30 x 1
DUF-AG-10201	10 x 20 x 1	DUF-AG-16321	16 x 32 x 1
DUF-AG-10241	10 x 24 x 1	DUF-AG-16361	16 x 36 x 1
DUF-AG-10301	10 x 30 x 1	DUF-AG-18181	18 x 18 x 1
DUF-AG-12121	12 x 12 x 1	DUF-AG-18201	18 x 20 x 1
DUF-AG-12201	12 x 20 x 1	DUF-AG-18241	18 x 24 x 1
DUF-AG-12241	12 x 24 x 1	DUF-AG-18251	18 x 25 x 1
DUF-AG-12251	12 x 25 x 1	DUF-AG-18301	18 x 30 x 1
DUF-AG-12301	12 x 30 x 1	DUF-AG-18361	18 x 36 x 1
DUF-AG-12361	12 x 36 x 1	DUF-AG-19271	19 x 27 x 1
DUF-AG-14141	14 x 14 x 1	DUF-AG-20201	20 x 20 x 1
DUF-AG-14201	14 x 20 x 1	DUF-AG-20241	20 x 24 x 1
DUF-AG-14241	14 x 24 x 1	DUF-AG-20251	20 x 25 x 1
DUF-AG-14251	14 x 25 x 1	DUF-AG-20301	20 x 30 x 1
DUF-AG-14301	14 x 30 x 1	DUF-AG-20321	20 x 32 x 1
DUF-AG-15201	15 x 20 x 1	DUF-AG-21211	21 x 21 x 1
DUF-AG-15251	15 x 25 x 1	DUF-AG-24241	24 x 24 x 1
DUF-AG-16161	16 x 16 x 1	DUF-AG-24301	24 x 30 x 1
DUF-AG-16201	16 x 20 x 1	DUF-AG-25251	25 x 25 x 1
DUF-AG-16241	16 x 24 x 1	DUF-AG-CUSTOM	CUSTOM - Specify size in order notes.
DUF-AG-16251	16 X 25 X 1		

MAX AIRE

PART NO.	DESCRIPTION
DUF-MA-100200	10 x 20 x 1
DUF-MA-100300	10 x 30 x 1
DUF-MA-120120	12 x 12 x 1
DUF-MA-120200	12 x 20 x 1
DUF-MA-120240	12 X 24 X 1
DUF-MA-120300	12 x 30 x 1
DUF-MA-120360	12 x 36 x 1
DUF-MA-140140	14 x 14 x 1
DUF-MA-140200	14 x 20 x 1
DUF-MA-140240	14 x 24 x 1
DUF-MA-140250	14 x 25 x 1
DUF-MA-140300	14 x 30 x 1
DUF-MA-14300	14 x 30 x 1
DUF-MA-160160	16 x 16 x 1
DUF-MA-160200	16 x 20 x 1
DUF-MA-160240	16 x 24 x 1
DUF-MA-160250	16 x 25 x 1
DUF-MA-160300	16 x 30 x 1
DUF-MA-1CUSTOM	CUSTOM - Specify size in order notes.
DUF-MA-200200	20 x 20 x 1
DUF-MA-200240	20 x 24 x 1
DUF-MA-200250	20 x 25 x 1
DUF-MA-200300	20 x 30 x 1
DUF-MA-240240	24 x 24 x 1
DUF-MA962025	20 x 25 Adj.
DUF-MA962430	24 x 30 Adj.

DUSTFREE 95


PART NO.	DESCRIPTION	PART NO.	DESCRIPTION	PART NO.	DESCRIPTION	PART NO.	DESCRIPTION
DUF-95-10X10X1	10 x 10 x 1	DUF-95-14X14X3/4	14 x 14 x 3/4	DUF-95-16X30X2	16 x 30 x 2	DUF-95-20X24X1	20 x 24 x 1
DUF-95-10X10X2	10 x 10 x 2	DUF-95-14X20X1	14 x 20 x 1	DUF-95-16X30X3/4	16 x 30 x 3/4	DUF-95-20X24X2	20 x 24 x 2
DUF-95-10X10X3/4	10 x 10 x 3/4	DUF-95-14X20X2	14 x 20 x 2	DUF-95-16X32X1	16 x 32 x 1	DUF-95-20X24X3/4	20 x 24 x 3/4
DUF-95-10X20X1	10 x 20 x 1	DUF-95-14X20X3/4	14 x 20 x 3/4	DUF-95-16X32X2	16 x 32 x 2	DUF-95-20X25X1	20 x 25 x 1
DUF-95-10X20X2	10 x 20 x 2	DUF-95-14X24X1	14 x 24 x 1	DUF-95-16X32X3/4	16 x 32 x 3/4	DUF-95-20X25X2	20 x 25 x 2
DUF-95-10X20X3/4	10 x 20 x 3/4	DUF-95-14X24X2	14 x 24 x 2	DUF-95-16X36X1	16 x 36 x 1	DUF-95-20X25X3/4	20 x 25 x 3/4
DUF-95-10X24X1	10 x 24 x 1	DUF-95-14X24X3/4	14 x 24 x 3/4	DUF-95-16X36X2	16 x 36 x 2	DUF-95-20X30X1	20 x 30 x 1
DUF-95-10X24X2	10 x 24 x 2	DUF-95-14X25X1	14 x 25 x 1	DUF-95-16X36X3/4	16 x 36 x 3/4	DUF-95-20X30X2	20 x 30 x 2
DUF-95-10X24X3/4	10 x 24 x 3/4	DUF-95-14X25X2	14 x 25 x 2	DUF-95-18X18X1	18 x 18 x 1	DUF-95-20X30X3/4	20 x 30 x 3/4
DUF-95-10X30X1	10 x 30 x 1	DUF-95-14X25X3/4	14 x 25 x 3/4	DUF-95-18X18X2	18 x 18 x 2	DUF-95-20X32X1	20 x 32 x 1
DUF-95-10X30X2	10 x 30 x 2	DUF-95-14X30X1	14 x 30 x 1	DUF-95-18X18X3/4	18 x 18 x 3/4	DUF-95-20X32X2	20 x 32 x 2
DUF-95-10X30X3/4	10 x 30 x 3/4	DUF-95-14X30X2	14 x 30 x 2	DUF-95-18X20X1	18 x 20 x 1	DUF-95-20X32X3/4	20 x 32 x 3/4
DUF-95-12X12X1	12 x 12 x 1	DUF-95-14X30X3/4	14 x 30 x 3/4	DUF-95-18X20X2	18 x 20 x 2	DUF-95-21X21X1	21 x 21 x 1
DUF-95-12X12X2	12 x 12 x 2	DUF-95-15X20X1	15 x 20 x 1	DUF-95-18X20X3/4	18 x 20 x 3/4	DUF-95-21X21X2	21 x 21 x 2
DUF-95-12X12X3/4	12 x 12 x 3/4	DUF-95-15X20X2	15 x 20 x 2	DUF-95-18X24X1	18 x 24 x 1	DUF-95-21X21X3/4	21 x 21 x 3/4
DUF-95-12X20X1	12 x 20 x 1	DUF-95-15X20X3/4	15 x 20 x 3/4	DUF-95-18X24X2	18 x 24 x 2	DUF-95-24X24X1	24 x 24 x 1
DUF-95-12X20X2	12 x 20 x 2	DUF-95-15X25X1	15 x 25 x 1	DUF-95-18X24X3/4	18 x 24 x 3/4	DUF-95-24X24X2	24 x 24 x 2
DUF-95-12X20X3/4	12 x 20 x 3/4	DUF-95-15X25X2	15 x 25 x 2	DUF-95-18X25X1	18 x 25 x 1	DUF-95-24X24X3/4	24 x 24 x 3/4
DUF-95-12X24X1	12 x 24 x 1	DUF-95-15X25X3/4	15 x 25 x 3/4	DUF-95-18X25X2	18 x 25 x 2	DUF-95-24X30X1	24 x 30 x 1
DUF-95-12X24X2	12 x 24 x 2	DUF-95-16X16X1	16 x 16 x 1	DUF-95-18X25X3/4	18 x 25 x 3/4	DUF-95-24X30X2	24 x 30 x 2
DUF-95-12X24X3/4	12 x 24 x 3/4	DUF-95-16X16X2	16 x 16 x 2	DUF-95-18X30X1	18 x 30 x 1	DUF-95-24X30X3/4	24 x 30 x 3/4
DUF-95-12X25X1	12 x 25 x 1	DUF-95-16X16X3/4	16 x 16 x 3/4	DUF-95-18X30X2	18 x 30 x 2	DUF-95-25X25X1	25 x 25 x 1
DUF-95-12X25X2	12 x 25 x 2	DUF-95-16X20X1	16 x 20 x 1	DUF-95-18X30X3/4	18 x 30 x 3/4	DUF-95-25X25X2	25 x 25 x 2
DUF-95-12X25X3/4	12 x 25 x 3/4	DUF-95-16X20X2	16 x 20 x 2	DUF-95-18X36X1	18 x 36 x 1	DUF-95-25X25X3/4	25 x 25 x 3/4
DUF-95-12X30X1	12 x 30 x 1	DUF-95-16X20X3/4	16 x 20 x 3/4	DUF-95-18X36X2	18 x 36 x 2	DUF-95-CUSTOM1	1" CUSTOM SIZE - Specify size in order notes.
DUF-95-12X30X2	12 x 30 x 2	DUF-95-16X24X1	16 x 24 x 1	DUF-95-18X36X3/4	18 x 36 x 3/4	DUF-95-CUSTOM2	2" CUSTOM SIZE - Specify size in order notes.
DUF-95-12X30X3/4	12 x 30 x 3/4	DUF-95-16X24X2	16 x 24 x 2	DUF-95-19X27X1	19 x 27 x 1	DUF-95-CUSTOM3/4	3/4" CUSTOM SIZE - Specify size in order notes.
DUF-95-12X36X1	12 x 36 x 1	DUF-95-16X24X3/4	16 x 24 x 3/4	DUF-95-19X27X2	19 x 27 x 2		
DUF-95-12X36X2	12 x 36 x 2	DUF-95-16X25X1	16 x 25 x 1	DUF-95-19X27X3/4	19 x 27 x 3/4		
DUF-95-12X36X3/4	12 x 36 x 3/4	DUF-95-16X25X2	16 x 25 x 2	DUF-95-20X20X1	20 x 20 x 1		
DUF-95-14X14X1	14 x 14 x 1	DUF-95-16X25X3/4	16 x 25 x 3/4	DUF-95-20X20X2	20 x 20 x 2	DUF-95-FT-20X25	FAST TRACK 20 X 25
DUF-95-14X14X2	14 x 14 x 2	DUF-95-16X30X1	16 x 30 x 1	DUF-95-20X20X3/4	20 x 20 x 3/4	DUF-95-FT-24X30	FAST TRACK 24 X 30

REPLACEMENT FILTERS

EZ FLEX REPLACEMENT FILTER

Some features include:

- EZ to assemble
 - saves up to 99% on assembly time
 - no combs
- Flexible (replaces competitors)
 - MPKA media cabinet
 - MACA media cabinet
 - Honeywell, Space-Guard, Trion
- MERV 10
- Patent pending



P4349

Kits (Expandable Filter + Plastic End Caps):

EXPXXUNV = Universal Kit that fits:

- Carrier MACA
- Honeywell F100E/F150E/F200E
- Trion Air Bear
- Research Products (Space-Gard 2200)
- New WeatherMaker® 8000 Platform

EXPXXLMC = Furnace Media Cabinet Kit that fits:

- Carrier Furnace Media Cabinets
- Carrier MPKA

Replacements (Expandable Filters only):

Can use end caps from old filter.

EXPXXFIL: Replacement Filters only - 10 pack

MEDIA AIR CLEANER	NOMINAL SIZE	EXPXXUNV		EXPXXLMC		
		0016	0020	0016	0020	0024
Carrier MACA	16 x 25	X				
	20 x 25		X			
Carrier MPKA	16 x 25			X		
	20 x 25				X	
	24 x 25					X
Space-Gard® 2200	20 x 25		X			
Honeywell F35 Expandapac	16 x 25	X				
	20 x 25		X			
Honeywell F100F	16 x 25	X				
	20 x 25		X			
Honeywell F150E	16 x 25	X				
	20 x 25		X			
Honeywell F200E	16 x 25	X				
	20 x 25		X			
Trion® Air Bear	16 x 25	X				
	20 x 25		X			
EXPXXFIL0016*	16 x 25	X		X		
EXPXXFIL0020*	20 x 25		X		X	
EXPXXFIL0024*	24 x 25					X

*These filters are direct replacements for EZ FLEX filter assemblies.

PART NO.	DESCRIPTION
EXPXXFIL0016	EZFLEX EXPANDABLE FILTER
EXPXXFIL0020	EZFLEX EXPANDABLE FILTER
EXPXXFIL0024	EZFLEX EXPANDABLE FILTER
EXPXXLMC0016	EZFLEX EXPANDABLE FILTER + PLASTIC END CAP
EXPXXLMC0020	EZFLEX EXPANDABLE FILTER + PLASTIC END CAP
EXPXXLMC0024	EZFLEX EXPANDABLE FILTER + PLASTIC END CAP
EXPXXUNV0016	EZFLEX EXPANDABLE FILTER + PLASTIC END CAP
EXPXXUNV0020	EZFLEX EXPANDABLE FILTER + PLASTIC END CAP

EZ FLEX GRILLES AND BASES

EZ FLEX FILTER CABINET

The New Totaline® EZ FLEX Filter Cabinet is available in six sizes, four vertical models 14 in. x 25 in. with wide flange to fit 14-in. wide furnace, 16 in. x 25 in. to fit 17-in. furnace, 20 in. x 25 in. to fit 20-in. furnace, 24 in. x 24 in. to fit 24-in. furnace. Vertical model EZ FLEX housings are designed to fit the new Heatwave 80 furnaces. Totaline EZ FLEX Filter Cabinets provide easy access for filter changes, and having the EZ FLEX filter as the replacement for this cabinet will save you time with its quick and easy assembly.

FEATURES:

- Fully insulated cabinet, 18 ga. steel with powder paint finish.
- Easy access hinged door and EZ FLEX filter makes for quick and easy filter change.
- Can be purchased with or without EZ FLEX filter.

DIMENSIONS:

FILTER CABINET MODEL NO.	FILTER SIZE (in.)	EZ FLEX KIT*	EZ FLEX MEDIA ONLY**
SIDE RETURN PAINTED CABINET WITHOUT FILTER			
EZF1625SRP	16 x 25	EXPXXUNV0016	EXPXXFIL0016
EZF2025SRP	20 x 25	EXPXXUNV0020	EXPXXFIL0020
SIDE RETURN PAINTED CABINET WITH FILTER			
EZF1625SRP-WR	16 X 25	EXPXXUNV0016	EXPXXFIL0016
EZF2025SRP-WF	20 x 25	ESPXXUNV0020	EXPXXFIL0020
UPFLOW PAINTED CABINET WITHOUT FILTER			
EZF1425UFP	14 x 25	EXPXXUNV0016	EXPXXFIL0016
EZF1625UFP	16 x 25	EXPXXUNV0016	EXPXXFIL0016
EZF2025UFP	20 x 25	EXPXXUNV0020	EXPXXFIL0020
EZF2424UFP	24 x 24	EXPXXUNV0024	EXPXXFIL0024
UPFLOW PAINTED CABINET WITH FILTER			
EZF1425UFP-WF	14 x 25	EXPXXUNV0016	EXPXXFIL0016
EZF1625UFP-WF	16 x 25	EXPXXUNV0016	EXPXXFIL0016
EZF2025UFP-WR	20 x 25	EXPXXUNV0020	EXPXXFIL0020
EZF2424UFP-WF	24 x 24	EXPXXUNV0024	EXPXXFIL0024

*The EZ-Flex kit includes the plastic end panels in the box.

**The media only can be used only if the filter has the end panels from a previous installation. These filters are direct replacements for EZ-Flex filter assemblies.

EZ FLEX FEATURES:



- MERV 10.
- EZ to assembly, no combs.
- Patent Pending.

SPECIFICATIONS:

Material: 18 ga. steel construction.

Construction: Fully insulated cabinet with hinged door for easy access, high quality latch and gasket on door creates a tight seal.

Finish: Powder paint, grey.



FILTER CABINET MODEL NO.	A	B	C	D	E	F	G	H	I
SIDE RETURN CABINET									
EZF1625SRP	1.375 in. (.35 cm)	24 in. (61 cm)	14.625 in. (37 cm)	1.375 in. (.35 cm)	26 in. (66 cm)	1 in. (.26 cm)	17.375 in. (44.1 cm)	1 in. (.26 cm)	—
EZF2025SRP	1.375 in. (.35 cm)	24 in. (61 cm)	18.625 in. (47.3 cm)	1.375 in. (.35 cm)	26 in. (66 cm)	1 in. (.26 cm)	21.375 in. (54.2 cm)	1 in. (.26 cm)	—
UPFLOW CABINET									
EZF1425UFP	2.875 in. (.73 cm)	22.25 in. (56.5 cm)	12.625 in. (32 cm)	2.875 in. (.73 cm)	29 in. (73.6 cm)	5.75 in. (14.6 cm)	17.375 in. (44.1 cm)	1 in. (.26 cm)	5.875 in. (14.9 cm)
EZF1625UFP	1.375 in. (.35 cm)	22.25 in. (56.5 cm)	14.625 in. (37 cm)	1.375 in. (.35 cm)	29 in. (73.6 cm)	5.75 in. (14.6 cm)	17.375 in. (44.1 cm)	1 in. (.26 cm)	5.875 in. (14.9 cm)
EZF2025UFP	1.375 in. (.35 cm)	22.25 in. (56.5 cm)	18.625 in. (47.3 cm)	1.375 in. (.35 cm)	29 in. (73.6 cm)	5.75 in. (14.6 cm)	21.375 in. (54.2 cm)	1 in. (.26 cm)	5.875 in. (14.9 cm)
EZF2425UFP	1.375 in. (.35 cm)	22.25 in. (56.5 cm)	22.625 in. (57.4 cm)	1.375 in. (.35 cm)	29 in. (73.6 cm)	5.75 in. (14.6 cm)	25.375 in. (64.4 cm)	1 in. (.26 cm)	5.875 in. (14.9 cm)

EZ FLEX GRILLES AND BASES

EZ FLEX RETURN AIR FILTER GRILLE

The New Totaline® EZ FLEX Return Air Filter Grille is designed for both commercial and residential applications. It provides easy access for filter changes, and having the EZ FLEX filter as the replacement for this cabinet will save you time with its quick and easy assembly. Nominal sizes available are for 16 in. x 25 in. and 20 in. x 25 in. filter.

FEATURES:


- Attractive white aluminum, easy to wipe clean.
- Wide margin for easy wall or ceiling installation.
- Conealed hinges for neat appearance, hinged face fits flush with frame.

SPECIFICATIONS:

Material: Extruded and rolled aluminum.

Face: Extruded frame with miter/welded corners. Individual extruded bars horizontally set on 3/4-in. centers and fixed at a 45 degree angle of deflection.

Finish: EDP white.




P4431

FILTER GRILLE CABINET MODEL	FILTER SIZE (in.)	EZ FLEX KIT*	EZ FLEX MEDIA ONLY**
P907-RAG-EZF-1625	16 x 25	EXPXXUNV0016	EXPXXFIL0016
P907-RAG-EZF-2025	20 x 25	EXPXXUNV0020	EXPXXFIL0020

*The EZ FLEX kit includes the plastic end panels in the box.

**The media only can be used only if the filter has the end panels from a previous installation. These filters are direct replacements for EZ FLEX filter assemblies.

FILTER GRILLE CABINET MODEL	A	B	C	D	E
P907-RAG-EZF-1625	16 in. (40.5 cm)	25 in. (63.5 cm)	1/4 in. (.63 cm)	5 in. (12.7 cm)	3/4 in. (.19 cm)
P907-RAG-EZF-2025	20 in. (51 cm)	26 in. (66 cm)	5 in. (12.7 cm)	1/4 in. (.63 cm)	3/4 in. (.19 cm)



P4431A